

Standard Pulp Disintegrator (PL28-2)



1. Description:

PL28-2 standard pulp disintegrator is vertical type, it dissociates the fibers in the pulp by high rotary speed. It is used for hand sheet forming, the measurement of freeness and material selection etc.

This machine conforms to the standards of JIS-P8220, TAPPI-T205, ISO-5263. Simple to operate, reliable, cover sealed, transparent container using ductile materials, visible in mixing process.

2. Specification:

2.1 Specimen: dry pulp 24g, consistency 1.2%, solution 2000ml;

2.2 Power supply: 370W, 380V;

2.3 Container volume: 3.46L;



شرکت دقیق پرتو
تامین کننده تجهیزات آزمایشگاهی و کنترل کیفی

۰۲۱-۶۶۹۳۷۲۱۴

- 2.4 Pulp volume: 2000MI;
- 2.5 Propeller diameter: 90mm;
- 2.6 Rotary speed: 3000r/min \pm 5r/min;
- 2.7 Standard rpm: 50000r (settable)
- 2.8 Weight: 90kg



دقیق پرتو
DAGHIGH PARTO

آزمایشگاه تخصصی میکروبیولوژی

شرکت دقیق پرتو
تامین کننده تجهیزات آزمایشگاهی و کنترل کیفی

۰۲۱-۶۶۹۳۷۲۱۴